

# Eaton AR631 S22

Catalog Number: AR631 S22

Eaton Crouse-Hinds series Arktite AR receptacle, 60A, Three-wire, three-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, Reversed contacts, 600 Vac/250 Vdc

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AR receptacle	AR631 S22
	UPC
	782274419213
Product Length/Depth	Product Height
4.25 in	4.25 in
Product Width	Product Weight
4.25 in	2.3 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 1

### Configuration

Three-wire, three-pole

### Receptacle style

Spring door

### Material

Copper-free aluminum

### Special features

Reversed contacts

## Resources

### Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(AR\)](#)

### Installation instructions

[IF 1229 - Arktite Plugs and Receptacles, Model M4, 30, 60, 100A](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - AR631 S22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)