

Eaton ARE2211

Catalog Number: ARE2211

Eaton Crouse-Hinds series Arktite ARE receptacle assembly, 20A, Two-wire, two-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 1/2", 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARE receptacle assembly	ARE2211
	UPC
	782274040479
Product Length/Depth	Product Height
4.875 in	6.875 in
Product Width	Product Weight
4.25 in	2 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

20A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Two-wire, two-pole

Trade size

1/2"

Receptacle style

Spring door

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ARE2211 3D drawing](#)

Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - ARE2211](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)