

# Eaton ARE2212

Catalog Number: ARE2212

Eaton Crouse-Hinds series Arktite ARE receptacle assembly, 20A, Two-wire, two-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 3/4", 600 Vac/250 Vdc



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARE receptacle assembly	ARE2212
	UPC
	782274040486
Product Length/Depth	Product Height
4.875 in	6.875 in
Product Width	Product Weight
4.25 in	2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

## Product specifications

### Amperage Rating

20A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 1

### Configuration

Two-wire, two-pole

### Trade size

3/4"

### Receptacle style

Spring door

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds ARE2212 3D drawing](#)

### Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Installation instructions

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - ARE2212](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)