

Eaton ARE3313

Catalog Number: ARE3313

Eaton Crouse-Hinds series Arktite ARE receptacle assembly, 30A, Three-wire, three-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 1", 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARE receptacle assembly	ARE3313
	UPC
	782274040554
Product Length/Depth	Product Height
5.44 in	7.19 in
Product Width	Product Weight
4.25 in	2.95 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

30A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Three-wire, three-pole

Trade size

1"

Receptacle style

Spring door

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ARE3313 3D drawing](#)

Catalogs

[Arktite 30A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - ARE3313](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)