

# Eaton ARE6314

Catalog Number: ARE6314

Eaton Crouse-Hinds series Arktite ARE receptacle assembly, 60A, Three-wire, three-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 1-1/4", 600 Vac/250 Vdc



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARE receptacle assembly	ARE6314
	UPC
	782274040660
Product Length/Depth	Product Height
6.19 in	9.88 in
Product Width	Product Weight
5.25 in	4.4 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 1

### Configuration

Three-wire, three-pole

### Trade size

1-1/4"

### Receptacle style

Spring door

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds ARE6314 3D drawing](#)

### Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - ARE6314](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)