

Eaton AREA10425

Catalog Number: AREA10425

Eaton Crouse-Hinds series Arktite AREA receptacle assembly, 100A, Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Spring door, 1-1/2", 600 Vac/250 Vdc

General specifications




Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AREA receptacle assembly	AREA10425
	UPC 782274034928
Product Length/Depth	Product Height
9.88 in	10.5 in
Product Width	Product Weight
5.88 in	8.1 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

100A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Trade size

1-1/2"

Receptacle style

Spring door

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds AREA10425 3D drawing](#)

Catalogs

[Arkrite 100A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arkrite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - AREA10425](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)