

Eaton AREA6313

Catalog Number: AREA6313

Eaton Crouse-Hinds series Arktite AREA receptacle assembly, 60A, Three-wire, three-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 1", 600 Vac/250 Vdc

General specifications




Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AREA receptacle assembly	AREA6313
	UPC 782274040783
Product Length/Depth	Product Height
8.88 in	9.44 in
Product Width	Product Weight
5.88 in	7.1 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

60A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Three-wire, three-pole

Trade size

1"

Receptacle style

Spring door

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds AREA6313 3D drawing](#)

Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - AREA6313](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)