

Eaton ARL2041 S22

Catalog Number: ARL2041 S22

Eaton Crouse-Hinds series Arktite ARL receptacle, 200A, Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, Reversed contacts, Mechanical lug, 600 Vac/250 Vdc, 0.687"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARL receptacle	ARL2041 S22
	UPC
	662276003972
Product Length/Depth	Product Height
7.5 in	6.63 in
Product Width	Product Weight
6.63 in	11.05 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Product specifications

Amperage Rating

200A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Four-wire, four-pole

Receptacle style

Spring door

Termination style

Mechanical lug

Wire well size

0.687"

Material

Copper-free aluminum

Special features

Reversed contacts

Resources

Catalogs

[Arktite 200A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - ARL2041 S22](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)