

# Eaton ARL2042 S22

Catalog Number: ARL2042 S22

Eaton Crouse-Hinds series Arktite ARL receptacle, 200A, Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Spring door, Reversed contacts, Mechanical lug, 600 Vac/250 Vdc, 0.687"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite ARL receptacle	ARL2042 S22
	UPC
	782274243405
Product Length/Depth	Product Height
7.5 in	6.63 in
Product Width	Product Weight
6.63 in	10.7 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

## Product specifications

### Amperage Rating

200A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Receptacle style

Spring door

### Termination style

Mechanical lug

### Wire well size

0.687"

### Material

Copper-free aluminum

### Special features

Reversed contacts

## Resources

### Catalogs

[Arktite 200A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - ARL2042 S22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)