

# Eaton B2025SS4

Catalog Number: B2025SS4

Eaton B-Line series O.D. pipe/conduit clamp, 0.0590"H x 0.5"L x 1.25"W, Steel, 400 load, 1/4"-20 bolt/pin size, O.D pipe conduit clamp



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series O.D. pipe and conduit clamp	B2025SS4
	UPC
	781011613280
<b>Product Length/Depth</b>	<b>Product Height</b>
0.5 in	0.059 in
<b>Product Width</b>	<b>Product Weight</b>
1.25 in	0.09 lb
<b>Certifications</b>	
Not Applicable	

## Model

### Bolt/pin size

1/4"-20

### Special features

Safety factor of 5 Include combination recess

### Type

O.D pipe conduit clamp

## Load rating/capacity

### Load capacity

400 lbs

## Material/finish

### Material

Steel

## Resources

### Catalogs

[Pipe clamps and hangers catalog section](#)

### Specifications and datasheets

[Eaton Specification Sheet - B2025SS4](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)