

Eaton B27CGF45B057

Catalog Number: B27CGF45B057

Eaton definite purpose starter, 45 A, Coil: 208-240 V, 50/60 Hz, Common control wiring, NEMA Type 1 Enclosed, 45 A IFL, 40-57 FLA, Single-phase, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing



Photo is representative

General specifications

Product Name	Catalog Number
Eaton definite purpose starter	B27CGF45B057
UPC	Product Length/Depth
786685458441	6.67 in
Product Height	Product Width
13.27 in	7.64 in
Product Weight	Warranty
10.6 lb	1 year

Certifications

UL Recognized
CSA Certified

Amperage Rating

45A

Phase

Single-phase

Type

Non-reversing

Overload relay

40-57 FLA

Coil

208-240 Vac, 50/60 Hz

Control characteristics

Common control

Enclosure

NEMA type 1 enclosed

Inductive full load

45 A IFL

Overload range

40-57 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Model

Starter

Specifications and datasheets

Eaton Specification Sheet - B27CGF45B057