

# Eaton B3188-11{2}PLN

Catalog Number: B3188-11/2PLN

Eaton B-Line series U-bolt, 3.75" H x 1.5" D, Steel, 1144 load cap, 3/8"-16 rod size, 2.125" thread len, 750 temp, U-bolt with 4 hex nuts

## General specifications



Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-11/2PLN
UPC	Product Height
781011113162	3.75 in
Product Diameter	Product Weight
1.5 in	0.29 lb
Certifications	
UL Listed	

Photo is representative

## Application

Operating temperature - max  
750 °F

## Model

Thread length  
2.125 in

Thread/rod size  
3/8"-16

Type  
Standard u-bolt with 4 hex nuts

## Load rating/capacity

Load capacity  
1144 lb

## Material/finish

Material  
Steel

## Resources

### Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

### Specifications and datasheets

[Eaton Specification Sheet - B3188-11/2PLN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)