

Eaton B3188-11{2}ZN

Catalog Number: B3188-11/2ZN

Eaton B-Line series U-bolt, 3.75" H x 1.5" D, Steel, 1144 load, 3/8"-16 rod size, 2.125" thread len, 750 temp, U-bolt with 4 hex nuts

General specifications



Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-11/2ZN
UPC	Product Height
781011113179	3.75 in
Product Diameter	Product Weight
1.5 in	0.29 lb
Certifications	
UL Listed	

Photo is representative

Application

Operating temperature - max
750 °F

Model

Thread length
2.125 in

Thread/rod size
3/8"-16

Type
Standard u-bolt with 4 hex nuts

Load rating/capacity

Load capacity
1144 lb

Material/finish

Material
Steel

Resources

Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

Specifications and datasheets

[Eaton Specification Sheet - B3188-11/ZZN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)