

Eaton B3188-12PLN

Catalog Number: B3188-12PLN

Eaton B-Line series U-bolt, 16.63" H x 12" D, Steel, 7016 load, 7/8"-9 rod size, 4.25" thread len, 750 temp, U-bolt with 4 hex nuts

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-12PLN
UPC	Product Height
781011113568	16.63 in
Product Diameter	Product Weight
12 in	6.61 lb
Certifications	
UL Listed	

Application

Operating temperature - max
750 °F

Model

Thread length
4.25 in

Thread/rod size
7/8"-9

Type
Standard u-bolt with 4 hex nuts

Load rating/capacity

Load capacity
7016 lb

Material/finish

Material
Steel

Resources

Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

Specifications and datasheets

[Eaton Specification Sheet - B3188-12PLN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)