

# Eaton B3188-20ZN

Catalog Number: B3188-20ZN

Eaton B-Line series U-bolt, 23.63" H x 2" D, Steel, 9240 load 1"-8 rod size, 4.75" thread len, 750 temp, U-bolt with 4 hex nuts

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-20ZN
UPC	Product Height
781011113735	23.63 in
Product Diameter	Product Weight
20 in	14.58 lb
Certifications	
cUL Listed	

## Application

Operating temperature - max  
750 °F

## Model

Thread length  
4.75 in

Thread/rod size  
1"-8

Type  
Standard u-bolt with 4 hex nuts

## Load rating/capacity

Load capacity  
9240 lb

## Material/finish

Material  
Steel

## Resources

### Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

### Specifications and datasheets

[Eaton Specification Sheet - B3188-20ZN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)