

Eaton B3188-21}2PLN

Catalog Number: B3188-21/2PLN

Eaton B-Line series U-bolt, 4.75" H x 2.5" D, Steel, 2114 load, 1/2"-13 rod size, 3" thread len, 750 temp, U-bolt with 4 hex nuts

General specifications



Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-21/2PLN
UPC	Product Height
781011113247	4.75 in
Product Diameter	Product Weight
2.5 in	0.72 lb
Certifications	
UL Listed	

Photo is representative

Application

Operating temperature - max
750 °F

Model

Thread length
3 in

Thread/rod size
1/2"-13

Type
Standard u-bolt with 4 hex nuts

Load rating/capacity

Load capacity
2114 lb

Material/finish

Material
Steel

Resources

Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

Specifications and datasheets

[Eaton Specification Sheet - B3188-21/2PLN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)