

# Eaton B3188-30ZN

Catalog Number: B3188-30ZN

Eaton B-Line series standard U-bolt, 33.63" H x 3" D, Steel, 9240 Lbs load cap, 1"-8 thread/rod size, 4.75" thread length, 750 op temp

## General specifications



Product Name	Eaton B-Line series standard U-bolt	Catalog Number	B3188-30ZN
UPC	781011113810	Product Height	33.63 in
Product Diameter	30 in	Product Weight	20.3 lb
Certifications	cUL Listed		

Photo is representative

## Application

Operating temperature - max  
750 °F

## Model

Thread length  
4.75 in

Thread/rod size  
1"-8

Type  
Standard u-bolt with 4 hex nuts

## Load rating/capacity

Load capacity  
9240 lb

## Material/finish

Material  
Steel

## Resources

### Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

### Specifications and datasheets

[Eaton Specification Sheet - B3188-30ZN](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)