

Eaton B3188-3/4ZN

Catalog Number: B3188-3/4ZN

Eaton B-Line series U-bolt, 3.63" H x 0.75" D, Steel, 675load, 1/2"-13 rod size, 2.125" thread len, 750 temp, U-bolt with 4 hex nuts

General specifications



Product Name	Catalog Number
Eaton B-Line series standard U-bolt	B3188-3/4ZN
UPC	Product Height
781011113056	3.63 in
Product Diameter	Product Weight
0.75 in	0.11 lb
Certifications	
UL Listed	

Photo is representative

Application

Operating temperature - max
750 °F

Model

Thread length
2.125 in

Thread/rod size
1/2"-13

Type
Standard u-bolt with 4 hex nuts

Load rating/capacity

Load capacity
675lb

Material/finish

Material
Steel

Resources

Catalogs

[pipe supports](#) [guides](#) [shields](#) [saddles](#) [section pipe hanger](#)

Specifications and datasheets

[Eaton Specification Sheet - B3188-3/4ZN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)