

Eaton B60NARNM

Catalog Number: B60NARNM

Eaton Air Conditioning Disconnect, Molded case switch, 60A, 120/240V, 10 kAIC, #14-2 Cu/Al 60°C or 75°C, NEMA 3R Polycarbonate enclosure, 10 hp at 240V, ANSI 61 gray

General specifications



Product Name

Eaton air conditioning disconnect

Catalog Number

B60NARNM

UPC

786676030175

Product Length/Depth

5 in

Product Height

8.63 in

Product Width

3.5 in

Product Weight

1.86 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
CSA Certified

Catalog Notes

For replacement molded case switch, order part number BR260NA.

Type

Air conditioning disconnect

Amperage Rating

60A

Horsepower

10 hp at 240 V

Voltage rating

120/240 V

Wire size

#14-2 AWG Cu/Al

Color

ANSI 61 gray

Enclosure

NEMA 3R

Enclosure material

Polycarbonate

Interrupt rating

10 kAIC

Brochures

[Air Conditioning Disconnects](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - B60NARNM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia