

Eaton BCH64BK

Catalog Number: BCH64BK

Eaton B-Line series datacomm and low voltage support fasteners, Capacity up to 300 4-Pair UTP 25 cat 5e or 2-strand Fiber Optic Cable or 185 CAT6 or 98 CAT6A, Cable hook, Wall mount, 4" Hook, 1 J-hook, Black, Load capacity of 30 lbs, Steel

General specifications



Product Name	Catalog Number
Eaton B-Line series cable hook color id clip	BCH64BK
	UPC
	782051473940
Product Length/Depth	Product Height
4.55 in	6.81 in
Product Width	Product Weight
2 in	0.56 lb
Certifications	
UL/CUL listed	

Photo is representative

Model

Type

Cable hook

Special features

Wall mount

Specifications

Load capacity

30 lb

Hook size

4 in

Number of J-hooks

1

Material/Finish

Material

Steel

Resources

Brochures

[J-Hook color ID clip flyer](#)

Catalogs

[Communications and low voltage section fastener catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - BCH64BK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)