

# Eaton BCH64CW

Catalog Number: BCH64CW

Eaton B-Line series datacomm and low voltage support fasteners, Capacity up to 300 4-Pair UTP 25 cat 5e or 2-strand Fiber Optic Cable or 185 CAT6 or 98 CAT6A, Cable hook, Wall mount, 1-4" J-hook, Computer white, Load capacity 30 lbs, Steel

## General specifications



Product Name	Catalog Number
Eaton B-Line series cable hook color id clip	BCH64CW
	UPC
	782051463910
Product Length/Depth	Product Height
4.55 in	6.81 in
Product Width	Product Weight
2 in	0.56 lb
Certifications	
UL/CUL listed	

Photo is representative

## Model

### Type

Cable hook

### Special features

Wall mount

## Specifications

### Load capacity

30 lb

### Hook size

4 in

### Number of J-hooks

1

## Material/Finish

### Material

Steel

## Resources

### Brochures

[J-Hook color ID clip flyer](#)

### Catalogs

[Communications and low voltage section fastener catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - BCH64CW](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)