

# Eaton BHP10385N

Catalog Number: BHP10385N

Eaton Crouse-Hinds series BHP plug, 100A, 0.875-1.375" cable diameter, Two-wire, three-pole, Brass contacts, 60-400 Hz, Style 2, Copper-free aluminum, 480 Vac

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series BHP plug	BHP10385N
UPC	Product Weight
782274041247	1 lb



Photo is representative

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 2

Class III

Class II, Division 1

Class I, Division 2

### NEMA Rating

3

4

7

9

12

## Product specifications

### Amperage Rating

100A

### Configuration

Two-wire, three-pole

### Cable diameter

0.875-1.375 in

### Grounding style

Style 2

### Voltage rating

480 Vac

### Frequency rating

60-400 Hz

### Material

Copper-free aluminum

### Contact material

Brass

## Resources

### Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

### Certification reports

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

### Installation instructions

[IF 119 - BHR Interlock Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - BHP10385N](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)