

Eaton BHP10487D

Catalog Number: BHP10487D

Eaton Crouse-Hinds series BHP plug, 100A, 1.375-1.875" cable diameter, Three-wire, four-pole, Brass, 60-400 Hz, Style 2, Copper-free aluminum, 480 Vac

General specifications



Product Name

Eaton Crouse-Hinds series BHP plug

Catalog Number

BHP10487D

UPC

782274045436

Product Length/Depth

10.43 in

Product Height

5 in

Product Width

5 in

Product Weight

5.2 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

12

Product specifications

Amperage Rating

100A

Configuration

Three-wire, four-pole

Cable diameter

1.375-1.875 in

Grounding style

Style 2

Voltage rating

480 Vac

Frequency rating

60-400 Hz

Material

Copper-free aluminum

Contact material

Brass

Resources

Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

Installation instructions

[IF 119 - BHR Interlock Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - BHP10487D](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)