

# Eaton BHP3383N

Catalog Number: BHP3383N

Eaton Crouse-Hinds series BHP plug, 30A, 0.500-0.875" cable diameter, Two-wire, three-pole, Brass, 60-400 Hz, Style 2, Copper-free aluminum, 480 Vac

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series BHP plug	BHP3383N
UPC	Product Length/Depth
782274041179	4.5 in
Product Height	Product Width
10.5 in	5 in
Product Weight	
5.21 lb	

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

12

## Product specifications

### Amperage Rating

30A

### Configuration

Two-wire, three-pole

### Cable diameter

0.500-0.875 in

### Grounding style

Style 2

### Voltage rating

480 Vac

### Frequency rating

60-400 Hz

### Material

Copper-free aluminum

### Contact material

Brass

## Resources

### Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

### Certification reports

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

### Installation instructions

[IF 119 - BHR Interlock Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - BHP3383N](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)