

Eaton BHRC10486D

Catalog Number: BHRC10486D

Eaton Crouse-Hinds series BHR interlocked receptacle with switch, 100A, Through feed, Three-wire, four-pole, Brass contacts, Style 2, Copper-free aluminum, Threaded cap, Factory sealed, 2", 480 Vac

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series BHR interlocked receptacle with switch	BHRC10486D
	UPC
	782274043289
Product Length/Depth	Product Height
6.5 in	27.25 in
Product Width	Product Weight
9.13 in	33 lb



Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

12

Product specifications

Enclosure type

With switch

Amperage Rating

100A

Configuration

Three-wire, four-pole

Trade size

2"

Receptacle style

Threaded cap

Back box style

Through feed

Grounding style

Style 2

Voltage rating

480 Vac

Material

Copper-free aluminum

Contact material

Brass

Special features

Factory sealed

Resources

Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

Certification reports

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

Installation instructions

[IF 119 - BHR Interlock Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - BHRC10486D](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)