

# Eaton BHRC6385N

Catalog Number: BHRC6385N

Eaton Crouse-Hinds series BHR interlocked receptacle with switch, 60A, Through feed, Two-wire, three-pole, Brass contacts, Style 2, Copper-free aluminum, Threaded cap, Factory sealed, 1-1/2", 480 Vac

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series BHR interlocked receptacle with switch	BHRC6385N
	<b>UPC</b>
	782274043869
<b>Product Length/Depth</b>	<b>Product Height</b>
6.5 in	27.25 in
<b>Product Width</b>	<b>Product Weight</b>
9.13 in	33.95 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

4

7

9

12

## Product specifications

### Enclosure type

With switch

### Amperage Rating

60A

### Configuration

Two-wire, three-pole

### Trade size

1-1/2"

### Receptacle style

Threaded cap

### Back box style

Through feed

### Grounding style

Style 2

### Voltage rating

480 Vac

### Material

Copper-free aluminum

### Contact material

Brass

### Special features

Factory sealed

## Resources

### Catalogs

[BHR and SRD Explosionproof Interlock Receptacles catalog page](#)

### Certification reports

[BHR and SRD Explosionproof Interlock Receptacles Canadian certification](#)

[BHR and SRD Explosionproof Interlock Receptacles UL certification](#)

### Installation instructions

[IF 119 - BHR Interlock Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - BHRC6385N](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)