

# Eaton BK{}AGC175{}1000R

Catalog Number: BK/AGC175/1000R

Eaton AGC series Fast-acting fuse 0.18A, , BK-AGC175-1000R



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series AGC fast-acting glass tube fuse	BK/AGC175/1000R
	<b>UPC</b>
	051712656238
<b>Product Length/Depth</b>	<b>Product Height</b>
1.25 in	0.25 in
<b>Product Width</b>	<b>Product Weight</b>
0.25 in	0.003 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked
	RoHS Compliant

**Type**

Electronic

**Application**

Electronic circuits

**Amperage Rating**

0.18A

**Used with**

out axial leads

**Fuse indicator**

Non-indicating

**Connection**

Ferrule end x ferrule end

**Response time**

60 min at 135%, 120 sec at 200%

**Quantity**

100

**Specifications and datasheets**[Eaton AGC fast-acting glass tube fuses data-sheet](#)[Eaton Specification Sheet - BK/AGC175/1000R](#)

Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)