

Eaton BK}GBB-1-R

Catalog Number: BK/GBB-1-R

Eaton GBB Series Very fast-acting fuse 1A, 250 Vac, 125 Vdc, BK-GBB-1-R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series very fast-acting fuse	BK/GBB-1-R
	UPC
	051712549745
EAN	Product Length/Depth
5027590226462	1.25 in
Product Height	Product Width
0.25 in	0.25 in
Product Weight	Warranty
0.006 lb	Not Applicable
Compliances	
RoHS Compliant	
CE Marked	

Type

Electronic

Application

Electronic circuits

Amperage Rating

1 A

Used with

out axial leads

Interrupt rating

200 AIC at 250 Vac

10 kAIC at 125 Vac/dc

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Response time

2 min at 150%, 1 sec at 250%

Material

Nickel-plated brass end cap construction

Ceramic tube

Quantity

100

Voltage rating

250 Vac, 125 Vdc

Specifications and datasheets

[Eaton GBB ceramic tube fuses data sheet](#)

[Eaton Specification Sheet - BK/GBB-1-R](#)