

Eaton BK}GBB-V-1-R

Catalog Number: BK/GBB-V-1-R

Eaton GBB Series Very fast-acting fuse 1A, 250 Vac, 125 Vdc, BK-GBB-V-1-R

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series very fast-acting fuse	BK/GBB-V-1-R
	UPC
	051712549530
EAN	Product Length/Depth
5027590246910	1.25 in
Product Height	Product Width
0.25 in	0.25 in
Product Weight	Warranty
0.007 lb	Not Applicable

Compliances

RoHS Compliant
CE Marked

Type

Electronic

Application

Electronic circuits

Amperage Rating

1 A

Used with

Axial leads

Interrupt rating

10 kAIC at 125 Vac/dc

200 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Response time

2 min at 150%, 1 sec at 250%

Material

Nickel-plated brass end cap construction

Ceramic tube

Quantity

100

Voltage rating

250 Vac, 125 Vdc

Specifications and datasheets[Eaton GBB ceramic tube fuses data sheet](#)[Eaton Specification Sheet - BK/GBB-V-1-R](#)