

Eaton BK{MDL-V-3-1}2-R

Catalog Number: BK/MDL-V-3-1/2-R

Eaton MDL Series Time-delay fuse 3.5A, 250 Vac, 32 Vdc (self certified), BK-MDL-V-3-1-2R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series MDL time-delay glass tube fuse	BK/MDL-V-3-1/2-R
	UPC
	051712652629
Product Length/Depth	Product Height
1.25 in	0.25 in
Product Width	Product Weight
0.25 in	0.007 lb
Warranty	Compliances
Not Applicable	RoHS Compliant
	CE Marked

Type

Electronic

Application

Electronic circuits

Amperage Rating

3.5 A

Used with

Axial leads

Interrupt rating

10 kAIC at 125 Vac

100 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Response time

60 min at 135%, 120 sec at 200%, 5 sec at 200%

Material

Glass tube

Nickel-plated brass end cap construction

Quantity

100

Voltage rating

250 Vac, 32 Vdc (self certified)

Specifications and datasheets

[Eaton MDL time delay glass tube fuses data sheet](#)

[Eaton Specification Sheet - BK/MDL-V-3-1/2-R](#)