

Eaton BK/S500-2-R

Catalog Number: BK/S500-2-R

Eaton S500 Series Fast-acting fuse 2A, 250 Vac or less, 32 Vdc (self certified), BK-S500-2-R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series S500 fast-acting fuse	BK/S500-2-R
	UPC
	051712643399
Product Height	Product Diameter
20 mm	5 mm
Product Weight	Warranty
0.68 g	Not Applicable
Compliances	Certifications
CCC Marked	VDE
CE Marked	
RoHS Compliant	

Type

Electronic

Application

Electronic circuits

Amperage Rating

2 A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

150 mV maximum

Interrupt rating

35 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Glass tube

Nickel-plated end-cap construction

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Specifications and datasheets

[Eaton S500 glass tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S500-2-R](#)