

Eaton BK/S500-V-32-R

Catalog Number: BK/S500-V-32-R

Eaton S500 Series Fast-acting fuse 32A, 250 Vac or less, 32 Vdc (self certified), BK-S500-V-32-R

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series S500 fast-acting fuse	BK/S500-V-32-R
	UPC
	051712642569
Product Length/Depth	Product Height
3.87 in	0.25 in
Product Width	Product Weight
0.25 in	0.005 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant
	CCC Marked
Certifications	
VDE	

defaultTaxonomyAttributeLabel

Type

Electronic

Application

Electronic circuits

Amperage Rating

32 A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

3200 mV maximum

Used with

Axial leads

Interrupt rating

35 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Glass tube

Nickel-plated end-cap construction

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Resources

Specifications and datasheets

[Eaton S500 glass tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S500-V-32-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)