

# Eaton BK/S500-V-63-R

Catalog Number: BK/S500-V-63-R

Eaton S500 Series Fast-acting fuse 0.063A, 250 Vac or less, 32 Vdc (self certified), BK-S500-V-63-R

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series S500 fast-acting fuse	BK/S500-V-63-R
	UPC
	051712642644
<b>Product Length/Depth</b>	<b>Product Height</b>
3.87 in	0.25 in
<b>Product Width</b>	<b>Product Weight</b>
0.25 in	0.005 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked
	CCC Marked
	RoHS Compliant
<b>Certifications</b>	
VDE	

## defaultTaxonomyAttributeLabel

### Type

Electronic

### Application

Electronic circuits

### Amperage Rating

0.063A

### Frequency rating - max

50 Hz

### Frequency rating - min

50 Hz

### Voltage drop

2000 mV maximum

### Used with

Axial leads

### Interrupt rating

35 AIC at 250 Vac

### Fuse indicator

Non-indicating

### Connection

Ferrule end x ferrule end

### Material

Silver-plated endcap construction

Glass tube

### Quantity

100

### Voltage rating

250 Vac or less, 32 Vdc (self certified)

## Resources

### Specifications and datasheets

[Eaton S500 glass tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S500-V-63-R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)