

Eaton BK/S500-V-6::3-R

Catalog Number: BK/S500-V-6.3-R

Eaton S500 Series Fast-acting fuse 6.30A, 250 Vac or less, 32 Vdc (self certified), BK-S500-V-6-3-R

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series S500 fast-acting fuse	BK/S500-V-6.3-R
	UPC
	051712642637
EAN	Product Length/Depth
5027590154819	3.87 in
Product Height	Product Width
0.25 in	0.25 in
Product Weight	Warranty
0.005 lb	Not Applicable
Compliances	Certifications
CCC Marked	VDE
CE Marked	
RoHS Compliant	

defaultTaxonomyAttributeLabel

Type

Electronic

Application

Electronic circuits

Amperage Rating

6.30A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

120 mV maximum

Used with

Axial leads

Interrupt rating

63 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Glass tube

Nickel-plated end-cap construction

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Resources

Specifications and datasheets

[Eaton Specification Sheet - BK/S500-V-6.3-R](#)

[Eaton S500 glass tube fuses data sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)