

Eaton BK/S501-63-R

Catalog Number: BK/S501-63-R

Eaton S501 Series Fast-acting fuse 0.063A, 250 Vac or less, 32 Vdc (self certified), BK-S501-63-R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series S501 fast-acting fuse	BK/S501-63-R
	UPC
	051712648226
Product Length/Depth	Product Height
0.984 in	0.197 in
Product Width	Product Weight
0.197 in	0.001 lb
Warranty	Compliances
Not Applicable	CE Marked
	CCC Marked
	RoHS Compliant
Certifications	
VDE	

Type

Electronic

Application

Electronic circuits

Amperage Rating

0.063A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

3300 mV typical

Interrupt rating

1.5 kAIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Silver-plated endcap construction

Ceramic tube

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Specifications and datasheets[Eaton Specification Sheet - BK/S501-63-R](#)[Eaton S501 ceramic tube fuses data sheet](#)