

Eaton BK/S501-6.3-R

Catalog Number: BK/S501-6.3-R

Eaton S501 Series Fast-acting fuse 6.30A, 250 Vac or less, 32 Vdc (self certified), BK-S501-6-3-R



Photo is representative

General specifications

Product Name Catalog Number

Eaton Bussmann series S501 fast-acting fuse BK/S501-6.3-R

UPC

051712648219

Product Length/Depth

0.984 in

Product Height

0.197 in

Product Width

0.197 in

Product Weight

0.001 lb

Warranty

Not Applicable

Compliances

CE Marked

RoHS Compliant

CCC Marked

Certifications

VDE



Powering Business Worldwide

Type

Electronic

Application

Electronic circuits

Amperage Rating

6.30A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

150 mV typical

Interrupt rating

1.5 kAIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Ceramic tube

Nickel-plated endcap construction

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Specifications and datasheets

[Eaton S501 ceramic tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S501-6.3-R](#)