

Eaton BK/S501-V-800-R

Catalog Number: BK/S501-V-800-R

Eaton S501 Series Fast-acting fuse 0.8A, 250 Vac or less, 32 Vdc (self certified), BK-S501-V-800-R

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series S501 fast-acting fuse	BK/S501-V-800-R

UPC
051712648400

Product Length/Depth
0.984 in

Product Height
0.197 in

Product Width
0.197 in

Product Weight
0.001 lb

Warranty
Not Applicable

Compliances
RoHS Compliant
CCC Marked
CE Marked

Certifications
VDE

defaultTaxonomyAttributeLabel

Type

Electronic

Application

Electronic circuits

Amperage Rating

0.8A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

490 mV typical

Used with

Axial leads

Interrupt rating

1.5 kAIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Nickel-plated endcap construction

Ceramic tube

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Resources

Specifications and datasheets

[Eaton Specification Sheet - BK/S501-V-800-R](#)

[Eaton S501 ceramic tube fuses data sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)