

Eaton BK/S501-V-80-R

Catalog Number: BK/S501-V-80-R

Eaton S501 Series Fast-acting fuse 0.08A, 250 Vac or less, 32 Vdc (self certified), BK-S501-V-80-R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series S501 fast-acting fuse	BK/S501-V-80-R
	UPC
	051712648417
Product Length/Depth	Product Height
0.984 in	0.197 in
Product Width	Product Weight
0.197 in	0.001 lb
Warranty	Compliances
Not Applicable	RoHS Compliant
	CE Marked
	CCC Marked
Certifications	
VDE	

defaultTaxonomyAttributeLabel

Type

Electronic

Application

Electronic circuits

Amperage Rating

0.08A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

2600 mV typical

Used with

Axial leads

Interrupt rating

1.5 kAIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Silver-plated endcap construction

Ceramic tube

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Resources

Specifications and datasheets

[Eaton S501 ceramic tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S501-V-80-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)