

Eaton BK/S506-160-R

Catalog Number: BK/S506-160-R

Eaton S506 Series Time-delay fuse 0.16A, 250 Vac or less, 32 Vdc (self certified), 35 AIC at 250 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series time-delay fuse	BK/S506-160-R
UPC	Product Length/Depth
051712649049	20 mm
Product Height	Product Width
5 mm	5 mm
Product Weight	Warranty
0.002 g	Not Applicable
Compliances	Certifications
RoHS Compliant	VDE
CCC Marked	

defaultTaxonomyAttributeLabel

Type

Electronic

Special features

Glass tube

Application

Electronic circuits

Amperage Rating

0.16A

Frequency rating - max

50 Hz

Frequency rating - min

50 Hz

Voltage drop

320 mV maximum

Interrupt rating

35 AIC at 250 Vac

Fuse indicator

Non-indicating

Connection

Ferrule end x ferrule end

Material

Glass tube

Nickel-plated brass end cap construction

Packaging type

Bulk

Quantity

100

Voltage rating

250 Vac or less, 32 Vdc (self certified)

Resources

Specifications and datasheets

[Eaton S506 time delay glass tube fuses data sheet](#)

[Eaton Specification Sheet - BK/S506-160-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)