

# Eaton BK/S506-50-R

Catalog Number: BK/S506-50-R

Eaton S506 Series Time-delay fuse 0.05A, 250 Vac or less, 32 Vdc (self certified), 35 AIC at 250 Vac



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Bussmann series time-delay fuse	BK/S506-50-R
UPC	Product Length/Depth
051712649179	20 mm
Product Height	Product Width
5 mm	5 mm
Product Weight	Warranty
0.002 g	Not Applicable
Compliances	Certifications
RoHS Compliant	VDE
CCC Marked	

## defaultTaxonomyAttributeLabel

### Type

Electronic

### Special features

Glass tube

### Application

Electronic circuits

### Amperage Rating

0.05A

### Frequency rating - max

50 Hz

### Frequency rating - min

50 Hz

### Voltage drop

800 mV maximum

### Interrupt rating

35 AIC at 250 Vac

### Fuse indicator

Non-indicating

### Connection

Ferrule end x ferrule end

### Material

Glass tube

Nickel-plated brass end cap construction

### Packaging type

Bulk

### Quantity

100

### Voltage rating

250 Vac or less, 32 Vdc (self certified)

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BK/S506-50-R](#)

[Eaton S506 time delay glass tube fuses data sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)