

# Eaton BK/S506-V-160-R

Catalog Number: BK/S506-V-160-R

Eaton S506 Series Time-delay fuse 0.16A, 250 Vac or less, 32 Vdc (self certified)

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann series time-delay fuse	BK/S506-V-160-R

UPC	EAN
051712649292	5027590210942

Product Length/Depth	Product Height
20 mm	5 mm

Product Width	Product Weight
5 mm	0.002 g

Warranty	Compliances
Not Applicable	CCC Marked
	RoHS Compliant

Certifications  
VDE

**Type**

Electronic

**Special features**

Glass tube

**Application**

Electronic circuits

**Amperage Rating**

0.16A

**Frequency rating - max**

50 Hz

**Frequency rating - min**

50 Hz

**Voltage drop**

320 mV maximum

**Used with**

Axial leads

**Interrupt rating**

35 AIC at 250 Vac

**Fuse indicator**

Non-indicating

**Connection**

Ferrule end x ferrule end

**Material**

Glass tube

Nickel-plated brass end cap construction

**Packaging type**

Bulk

**Quantity**

100

**Voltage rating**

250 Vac or less, 32 Vdc (self certified)

**Specifications and datasheets**

[Eaton Specification Sheet - BK/S506-V-160-R](#)

[Eaton S506 time delay glass tube fuses data sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)