

Eaton BK}SC-30

Catalog Number: BK/SC-30

Eaton Bussmann series SC fuse, Current-limiting time-delay fuse, Rejection style, 30 A, Class G, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 10 kAIC at 300 Vdc|100 kAIC at 480 Vac, Bulk, 480 V, 300 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series SC fuse	BK/SC-30
UPC	EAN
051712750905	5027590408349
Product Length/Depth	Product Height
0.41 in	1.62 in
Product Width	Product Weight
0.41 in	0.18 lb
Warranty	Compliances
Not Applicable	Not Applicable
	RoHS Compliant
Catalog Notes	
Bulk	

Electrical rating

Amperage Rating

30 A

Interrupt rating

10 kAIC at 300 Vdc

100 kAIC at 480 Vac

Response time

12 sec at 200%

Voltage rating

480 Vac, 300 Vdc

Physical details

Packaging type

Standard

Bulk

General information

Class

Class G

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Rejection style

Resources

Catalogs

[BK/SC-30~BK-SC-30~BUSS SC FUSE CLASS G](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - BK/SC-30](#)