

# Eaton BN16DN0AB

Catalog Number: BN16DN0AB

Eaton NEMA starter, Space SVG Starter, Ground fault, 24 Vdc Coil, Nema Size 0, 1-5 A



## General specifications

**Product Name**  
Eaton Freedom NEMA motor control starter

**Catalog Number**  
BN16DN0AB  
  
**UPC**  
782114023242

**Product Length/Depth**  
5.5 in

**Product Height**  
6.3 in

**Product Width**  
1.77 in

**Product Weight**  
1.12 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

### Catalog Notes

Heater Packs must be purchased separately. For separate 120V control circuit. For maximum hp at listed motor voltages, use the rating of other starters of same size.

Accessories

Freedom NEMA

Series

Freedom

Phase

Single-phase magnetic

Size

NEMA size 0

Voltage rating

120 V at 60 Hz

Horsepower

115 hp

Coil voltage

120 Vac

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - BN16DN0AB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)