

# Eaton BP{FRN-R-40

Catalog Number: BP/FRN-R-40

Eaton Bussmann series FRN-R fuse, Time-delay current-limiting fuse, 40 A, Dual, RK5, Non-indicating, Ferrule end x ferrule end, 11 sec at 500% at rated current, 20 kAIC Vdc|200 kAIC V, Blister pack



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	BP/FRN-R-40
UPC	Product Length/Depth
051712112062	3 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Compliances
0.272 lb	CE Marked

## Electrical rating

### Amperage Rating

40 A

### Interrupt rating

20 kAIC Vdc

200 kAIC Vac

### Response time

11 sec at 500% at rated current

## Physical details

### Number of elements

Dual

### Packaging type

Standard

Blister

## General information

### Class

Class RK5

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Rejection style

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[BP/FRN-R-40~BP/FRN-R-40~FUSETRON DUAL ELEM 1A3406](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - BP/FRN-R-40](#)