

Eaton BP/SC-20

Catalog Number: BP/SC-20

Eaton Bussmann series SC rejection fuse, rejection fuse, time delay, Current limiting, fast acting, Rejection style, 100A, 600 Vac, 170 Vdc, 100000A (RMS Symmetrical), 10000A (DC) interrupt rating, ferrule end x ferrule end connection



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Bussmann series SC rejection fuse	BP/SC-20
	UPC
	051712593120
Product Length/Depth	Product Height
1.31 in	0.41 in
Product Width	Product Weight
0.41 in	0.5 lb
Compliances	
Contact factory	
RoHS Compliant	

Electrical Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC Vdc

100 kAIC Vac

Voltage rating

600 Vac, 170 Vdc

General Information

Application

Fusible branch panelboards, HVAC branch circuit protection

Class

Class G

Connection

Ferrule end x ferrule end

Special features

Rejection style

Physical Details

Type

Time delay, current limiting, fast acting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[BP/SC-20~BP-SC-20~MIDGET FUSE](#)

Specifications and datasheets

[Eaton Specification Sheet - BP/SC-20](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)