

# Eaton BP{SC}-30

Catalog Number: BP/SC-30

Eaton Bussmann series SC rejection box, rejection fuse, time delay, Current limiting, fast acting, Rejection style, 20 A, 480 Vac, 300 Vdc, 100000A (RMS Symmetrical), 10000A (DC) interrupt rating, G class



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Bussmann series SC rejection box BP/SC-30	
UPC	Product Length/Depth
051712593137	1.31 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Compliances
0.5 lb	Contact factory
	RoHS Compliant

## Electrical Ratings

### Amperage Rating

30 A

### Interrupt rating

100 kAIC Vac

10 kAIC Vdc

### Voltage rating

480 Vac, 300 Vdc

## General Information

### Application

Fusible branch panelboards, HVAC branch circuit protection

### Class

Class G

### Connection

Ferrule end x ferrule end

### Special features

Rejection style

## Physical Details

### Type

Time delay, current limiting, fast acting

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[BP/SC-30~BP-SC-30~MIDGET FUSE](#)

### Specifications and datasheets

[Eaton Specification Sheet - BP/SC-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)