

# Eaton BR20B-BU

Catalog Number: BR20B-BU

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, Brown, Brass, High-impact nylon, PVC, 5-20R, Duplex, Screw, PVC



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton commercial specification grade duplex receptacle	BR20B-BU
	UPC
	032664736605
<b>Product Length/Depth</b>	<b>Product Height</b>
1.3 in	4.2 in
<b>Product Width</b>	<b>Product Weight</b>
0.88 in	0.21 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

### Application

Commercial

### Device grade

Commercial

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

PVC

### Color

Brown

### Connection type

Screw

### Allowable wire size

#14-10 AWG

### NEMA configuration

## Resources

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR20B-BU](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon

PVC

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)