

Eaton BRP120GF

Catalog Number: BRP120GF

Eaton BR GFCI circuit breaker, Plug-in ground fault circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, BRP, Trip-to-center, Plug-on, #14-8 AWG, Ground fault circuit interrupter, GFI, 5 mA

General specifications

Product Name	Catalog Number
Eaton BR GFCI circuit breaker	BRP120GF
UPC	Product Length/Depth
786689031206	4 in
Product Height	Product Width
1 in	3.5 in
Product Weight	Certifications
0.45 lb	Contact Manufacturer

defaultTaxonomyAttributeLabel

Type

Plug-in ground fault circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Trip Type

Trip-to-center

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Protection

5 mA

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BRP

Connection

Plug-on

Wire size

#14-8 AWG

Number of poles

Single-pole

Trip rating

20 A

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP120GF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)