

Eaton C0003P8TSES

Catalog Number: C0003P8TSES

Eaton, type AP, industrial control transformer, pv: 600v, taps: 2 at +2.5% fcan, 2 at -2.5% fcbn, sv: 120/240v, 115°C, 3000 va, cu magnet wire, elec. shield, frame: 292



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type AP industrial control transformer	C0003P8TSES
	UPC
	786680018459
Product Length/Depth	Product Height
9.567 in	9.764 in
Product Width	Product Weight
8.819 in	100 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Recognized
	Catalog Notes
	Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

292

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Wiring connection

405D

Performance Ratings

Primary voltage

600 V

Temperature rating

115°C

Volt ampere rating

3000 VA

Secondary voltage

120/240 V

Miscellaneous

Modification 1

Side/wall mounted

Special features

Electrostatically Shielded

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

[Transformer distribution catalog, volume 2, tab 2](#)

Specifications and datasheets

[Eaton Specification Sheet - C0003P8TSES](#)

[Transformer consulting application guide](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)