

Eaton C0005P7GB

Catalog Number: C0005P7GB

Eaton type AP, industrial control transformer, pv: 240 x 480v, taps: none, sv: 120/240v, 115°C, 5000 va, cu magnet wire, frame: 99



Photo is representative

General specifications

Product Name
Eaton Type AP industrial control transformer

Catalog Number

C0005P7GB

UPC

786680182013

Product Length/Depth

8.701 in

Product Height

10.748 in

Product Width

10.748 in

Product Weight

109 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Recognized from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Resin encapsulated, 60 Hz operation, 180°C insulation system, Convenient screw-type terminal board



Powering Business Worldwide

Physical Attributes

Coil material

Copper windings

Design

AP

Frame

99

Tap size

None

Wiring connection

416A

Performance Ratings

Primary voltage

240 x 480 V

Temperature rating

115°C

Volt ampere rating

5000 VA

Secondary voltage

120/240 V

Miscellaneous

Modification 1

Bottom mounted

Resources

Brochures

[Industrial control transformers brochure](#)

[dry-type distribution transformer-flex center line card](#)

Catalogs

[Transformer distribution catalog, volume 2, tab 2](#)

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Transformer consulting application guide](#)

[Eaton Specification Sheet - C0005P7GB](#)